



Novometer contour measuring gauge, Measuring range: 170-255mm



Order data

| | |
|--------------|----------------|
| Order number | 435170 170-255 |
| GTIN | 2050001951328 |
| Item class | 46D |

Description

Version:

Novometer contour measurement gauge for measuring internal diameters of round, oval or regular polygon bores. For measuring **resilient components**.

Note:

Version with digital display or with slip clutch for reproducible gauging force available on request. Version for measuring external diameters available on request. Stationary version with table available as a support for the workpiece. Novometer with reading of 0.01 mm available on request.

Technical description

| | |
|-----------------|------------------------|
| Scale divisions | 0.1 mm |
| Measuring range | 170 - 255 mm |
| Calibration | Price on request |
| Power supply | Mains operated |
| Type of product | Contour measuring tool |

Services

Calibration 3-point internal micrometer maximum
measuring range 300 mm

022500 300