



Endoscope probe, semi-rigid, 3.9 mm Ø, Probe length: 2000mm



Order data

Order number	492934 2000
GTIN	4045197806062
Item class	42L

Description

Version:

Sturdy watertight probe head (IP67) of stainless steel with dimmable white LEDs. Direction of view 0°.

Image aperture angle 56°.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

Ideal for inspection of voids where access is difficult, e.g. **automotive:** Engine, gearbox, fuel tank, bodywork, dashboard, appraisal. **Aerospace:** engines, turbines, pipework, and wiring systems. **Buildings:** Assessment of the structure of buildings, water damage, pest infestation. **Pipework systems:** weld seams, traces of foreign bodies, leaks. **Hydraulic systems:** cylinders, leaks. **Heating - sanitation - air conditioning:** ovens, furnaces, boilers, air conditioning systems, drainage systems. **Pest control:** Bees' nests, wasps' nests, birds' nests, insect entry points. **Police, customs:** Vehicle checking, goods checking.

Suitable for:

All endoscope versions No. 492923; 492924; 492925; 492928.

Optional extras:

Adapter No. 492896 for using the probes with photo / video endoscope No. 492890 size 2000.

Note:

Other types of probe (up to 30 m) with other probe head Ø and directions of view available on request.

Probe for pipework inspection:

- **Head Ø: 28 mm**
- **Probe length: 22 m**
- **Image aperture angle: 150°**
- **8 high-intensity LEDs.**

Technical description

Probe length	2000 mm
IP Index of Protection	IP 67
Camera resolution	320×240 px
Probe Ø	3.9 mm
Product name attribute	3.9 mm Ø
Type of product	Probe