

**Cordless staple gun, Manufacturer's designation: J214EA****Order data**

Order number	078409 J214EA
GTIN	4009729053683
Item class	07E

Description**Version:**

User-friendly, ergonomic professional staple guns for precision driving of round-wire and flat staples and nails.

- **Reload system in the base for quick and easy reloading.**
- **Distance stop for insertion of parallel rows of staples.**
- **Impact force control.**
- **Patented safety unlocking.**
- **Good access to restricted spaces.**
- **Staple supply viewing window.**

Handy cordless tacker with soft-touch handle. Wild shot prevention lock for greater safety. LED lamp for illuminating the working area.

Supplied with:

Includes an Li-ion battery, charger and transport case.

Note:

For suitable spare batteries see No. 078408.

Technical description

maximum staple insertion depth	14 mm
--------------------------------	-------

Manufacturer's designation	J-214
suitable type of staple	E, A
Weight	2.7 kg
Power supply	Rechargeable battery-powered
Type of product	Tacker

Accessories

Flat wire staples set 1200 pieces or 600 pieces maximum staple insertion depth 14 mm	078418 14
Nail set 1000 pieces or 2600 pieces maximum staple insertion depth 14 mm	078419 14
Round wire staples set 5000 pieces maximum staple insertion depth 8 mm	078417 8
Round wire staples set 5000 pieces maximum staple insertion depth 10 mm	078417 10
Round wire staples set 5000 pieces maximum staple insertion depth 6 mm	078417 6
Round wire staples set 5000 pieces maximum staple insertion depth 14 mm	078417 14
Li-ion battery Type N1,3	078408 N1,3