



Cordless nibbler, Type: 7132046



Order data

Order number	078109 7132046
GTIN	4014586886688
Item class	03F

Description

Version:

- **Flexible nibblers with high manoeuvrability for thin sheet metal, trapezoidal sheet, corrugated sheet and sections.**
- **Very economical operating costs due to long working life of die and matrix.**
- **QuickIN quick-change system for quick die and matrix changing without tools**
- **Working direction can be changed without tools.**

Cordless sheet metal nibbler for portable use.

- **Slim design ensures optimum handling even under difficult working conditions.**
- **Highly suitable for trapezoidal sheet up to 1.3 mm thick and up to 85 mm step depth.**

Supplied with:

Cordless lamp **without** battery and **without** charger.

Note:

See No. 073832 and No. 073845 for suitable batteries and chargers.

Packaging: Carrying case

suitable battery - supplier / battery type / voltage: Fein type E 18 V

Manufacturer's designation: ABLK 1.6E

Number of rechargeable batteries contained: 0

Type of rechargeable battery: Lithium-ion

Battery voltage: 18 V

maximum material thickness steel 400 N/mm²: 1.6 mm

maximum material thickness steel 800 N/mm²: 0.7 mm

Technical description

Radius of the smallest curve	30 mm
Battery voltage	18 V
Packaging	Carrying case
Manufacturer's designation	ABLK 1.6E
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Weight	2.1 kg
maximum material thickness steel 800 N/mm ²	0.7 mm
maximum vibration to EN	< 2.5 m/s ²
Cutting width	5 mm
Cutting speed	1.9 m/min
maximum material thickness steel 400 N/mm ²	1.6 mm
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Nibblers

Accessories

Battery starter set Type 9260430003	073832 9260430003
Battery charger Type FE80	073845 FE80
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073837 FE18
Battery charger Type FE50	073845 FE50
Li-ion battery Battery type, battery voltage FE18 V	073838 FE18
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18
Battery charger Type FE30	073845 FE30

