



## Cordless sheet metal slitters / shears, Type: 7130046



### Order data

Order number	078100 7130046
GTIN	
Item class	03F

### Description

#### Version:

Cordless sheet metal shears for mobile use.

#### Sheet metal shears.

- **Cuts well round curves with only minor sheet metal deformation.**
- **Comfortable and quick for seaming and cutting to length.**
- **For sheet metal up to 800 N/mm<sup>2</sup> and stainless steels.**
- **Four-way changeover blade: clean and burr-free cutting with low operating costs.**

#### Supplied with:

Cordless lamp **without** battery and **without** charger.

#### Note:

See No. 073832 and No. 073845 for suitable batteries and chargers.

### Technical description

Cutting width	0 mm
Battery voltage	18 V
Packaging	Carrying case

maximum vibration to EN	< 2.5 m/s <sup>2</sup>
maximum material thickness steel 400&nbsp;N/mm <sup>2</sup>	1.6 mm
suitable battery - supplier / battery type / voltage	Fein type E 18 V
Weight	2 kg
Cutting speed	5 - 8 m/min
Rate of strokes	4000 min <sup>-1</sup>
maximum material thickness steel 800&nbsp;N/mm <sup>2</sup>	1 mm
Radius of the smallest curve	15 mm
Manufacturer's designation	ABLS 18 1.6E
Number of rechargeable batteries contained	0
Type of rechargeable battery	Lithium-ion
Power supply	Rechargeable battery-powered
Type of product	Aviation snips

## Accessories

Li-ion battery Rechargeable battery type, battery voltage FE18 V	073837 FE18
Li-ion battery Rechargeable battery type, battery voltage FE18 V	073835 FE18