

 Mahr**Digital external groove caliper with rod type depth gauge, Measuring range: 150mm****Order data**

Order number	412772 150
GTIN	4059192057183
Item class	43A

Description**Version:**

Very large LCD display with 11 mm character height. Integral i-wi wireless data interface. Resistant to dust and moisture. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons. Service life approx. 3 years.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

i-wi radio receiver No. 498912.

Technical description

Scale divisions	0.0005 in
Error limit	0.03 mm
Scale divisions	0.01 mm
Jaw length	40 mm
Depth gauge	Ø 1.6
Measuring range	150 mm

Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Wireless application	Manufacturer's software
Standard	Manufacturer's standard
all parts	hardened
Material	Stainless steel, INOX
Reversible reading	mm / inch
Measured value saving	MAHR reference-lock system
Interface	MAHR i-wi radio system
Packaging	sturdy box
Calibration	A1
Measurement technology	digital
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
Radio receivers for Mahr i-wi Type STICK	498912 STICK