

 steinel**Heat gun, Type: 351601**

## Order data

Order number	078321 351601
GTIN	4007841351601
Item class	07E

## Description

### Version:

**High-quality heat gun HG 2520 EKF in pistol format** for professional applications, with carrying case. Electronically controlled with stepless regulation of the air quantity.

- **Connecting cable can be easily exchanged.**
- **Exchangeable ceramic heater with a service life of approx. 800 h.**
- **Air pressure of up to 4,000 Pa.**
- **Temperature can be set from 50 – 700°C using a joystick.**
- **Air volume controlled from 150 – 500 l/min.**
- **Safeguard against accidental restart.**
- **Cooling stage.**
- **LCD display and residual-heat indicator.**

### Application:

For welding and forming plastics, for shrinking, removing paints, soldering, drying, and thawing.

## Technical description

Weight	840 g
Air flow volume	150 - 500 l/min

Manufacturer's designation	HG 2520 EKF
Air temperature	50 - 700 °C
Power consumption	2300 W
Packaging	transport suitcase
Power supply	Mains operated
Type of product	Hot air pistol

---

## Accessories

Temperature scanner HG Scan PRO Type 007553	078325 007553
Temperature scanner HG Scan PRO Type 007690	078325 007690
Temperature scanner HL Scan Type 014919	078326 014919