

 steinel
Heat gun, Type: 351601



Order data

Order number	078321 351601
GTIN	4007841351601
Item class	07E

Description

Version:

High-quality heat gun HG 2520 EKF in pistol format for professional applications, with carrying case. Electronically controlled with stepless regulation of the air quantity.

- **Connecting cable can be easily exchanged.**
- **Exchangeable ceramic heater with a service life of approx. 800 h.**
- **Air pressure of up to 4,000 Pa.**
- **Temperature can be set from 50 – 700°C using a joystick.**
- **Air volume controlled from 150 – 500 l/min.**
- **Safeguard against accidental restart.**
- **Cooling stage.**
- **LCD display and residual-heat indicator.**

Application:

For welding and forming plastics, for shrinking, removing paints, soldering, drying, and thawing.

Technical description

Weight	840 g
Air flow volume	150 - 500 l/min

Manufacturer's designation	HG 2520 EKF
Air temperature	50 - 700 °C
Power consumption	2300 W
Packaging	transport suitcase
Power supply	Mains operated
Type of product	Hot air pistol

Accessories

Temperature scanner HG Scan PRO Type 007690	078325 007690
Temperature scanner HG Scan PRO Type 007553	078325 007553
Temperature scanner HL Scan Type 014919	078326 014919