

 steinel**Temperature scanner HG Scan PRO, Type: 007553****Order data**

Order number	078325 007553
GTIN	4007841007553
Item class	07E

Description**Version:**

Temperature scanner for sensing the temperature at the surface of the workpiece by means of infra-red measurement. Ideal determination of distance by laser. Acoustic and visual warning if the optimum temperature is overshoot or undershot. Setting in 10 °C steps.

HG Scan PRO with intelligent data exchange between the temperature scanner and hot-air blower. Power supply via the hot-air blower.

Complete temperature monitoring when working with temperature-sensitive workpieces. The HG Scan PRO senses the temperature at the surface of the workpiece by means of infra-red measurement. Ideal determination of distance by laser. Acoustic and visual warning if the optimum temperature is overshoot or undershot. Temperature recording range of 0 – 300°C, setting in 10°C steps.

Suitable for:

Suitable for heat gun HG 2620 E.

Technical description

Weight	120 g
suitable for	HG 2620

Temperature recording range	0 - 300 °C
Power supply	Mains operated
Type of product	Temperature scanner