

**Welder's mask, automatic optrel® vegaview2.5, Colour: BLACK**

---

**Order data**

Order number	097949 BLACK
GTIN	7640429870445
Item class	09U

---

**Description****Version:**

**Lightweight welder's mask, automatic** (482 g) for low stress on the head and neck muscles. With the best view and **100% protection against UV and IR radiation**. The mask has **true colour-rendition** and a shade level in the light state with high translucency of 23%, allowing a detailed clear view of the component. Simply pushing a button on the outside activates **grinding mode**. Ideal for poorly lit working environments. With comfortable headband with adjustment facility. The angle of perception of the electric arc can be adjusted using a slider; the sensitivity can also be adjusted for an ideal match to the working environment.

- **Shade levels: 8 – 12**
- **Shade level in the light state: 2.5**
- **With lithium 3 V battery (working life 3,000 hours)**
- **Field of view of the welding filter: 50 x 100 mm**

**Application:**

MIG/MAG welding. Stick welding, TIG welding, plasma welding and cutting

**Standard:**

EN 175; EN 379; EN 166

**Supplied with:**

1 outer visor, 1 storage bag

Switching time from bright to dark: 0.1 ms

Switching time from dark to bright: 50 - 1000 ms

Classification to EN 379: 1 / 1 / 1 / 2

---

## Technical description

Classification to EN 379	1 / 1 / 1 / 2
Switching time from dark to bright	50 - 1000 ms
Switching time from bright to dark	0.1 ms
Power supply	Battery-powered
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 CR2032
Type of product	Welder's mask

---

## Accessories

Visor set, 5 pieces internal	097963
Cotton sweatband set, 2 pieces	097965
Visor set, 2 pieces external	097962
Cotton sweatband set, 2 pieces (rear)	097975