

PRYOR

Numeral letter punch set, 27 pieces Normal script A – Z, &, Character height: 6mm



Order data

Order number	085430 6
GTIN	5022044003408
Item class	08W

Description

Version:

Made of hard and tough steel with particularly precise machine engraving and depth tolerance; accurately centred. Calibrated shank, through hardened. Striking head enhancement for safe working. Supplied in a plastic case.

High performance precision punches, chemically nickel-plated, very long service life.

Normal script; i. e. the punched character can be read directly on the component.

Application:

For punching into materials with a **strength up to 1200 N/mm²**.

Spare part:

Individual number punches under No. 085411 size font height/number, e. g. No. 085411 size 3/1.

Individual letter punches under No. 085431 size font height/character, e.g. No. 085431 size 3/A.

Note:

Other hand and machine punches of all types, such as punches with a company's logo etc., are available on request.

Technical description

Character height	6 mm
Shank thickness	9.5

overall length	70 mm
Type of product	Hand punch

Accessories

Letter punch – individualNormal script A – Z Character height / Characters 6/E mm	085431 6/E
Letter punch – individualNormal script A – Z Character height / Characters 6/F mm	085431 6/F
Punch holder Type GRIP	085475 GRIP
Letter punch – individualNormal script A – Z Character height / Characters 6/Y mm	085431 6/Y
Letter punch – individualNormal script A – Z Character height / Characters 6/R mm	085431 6/R
Letter punch – individualNormal script A – Z Character height / Characters 6/T mm	085431 6/T
Letter punch – individualNormal script A – Z Character height / Characters 6/K mm	085431 6/K
Letter punch – individualNormal script A – Z Character height / Characters 6/M mm	085431 6/M
Letter punch – individualNormal script A – Z Character height / Characters 6/U mm	085431 6/U
Letter punch – individualNormal script A – Z Character height / Characters 6/V mm	085431 6/V
Letter punch – individualNormal script A – Z Character height / Characters 6/I mm	085431 6/I
Letter punch – individualNormal script A – Z Character height / Characters 6/J mm	085431 6/J
Letter punch – individualNormal script A – Z Character height / Characters 6/S mm	085431 6/S
Letter punch – individualNormal script A – Z Character height / Characters 6/W mm	085431 6/W
	085431 6/O

Letter punch – individualNormal script A – Z Character
height / Characters 6/O mm

Letter punch – individualNormal script A – Z Character
height / Characters 6/A mm

085431 6/A

Letter punch – individualNormal script A – Z Character
height / Characters 6/X mm

085431 6/X

Letter punch – individualNormal script A – Z Character
height / Characters 6/& mm

085431 6/&

Letter punch – individualNormal script A – Z Character
height / Characters 6/N mm

085431 6/N

Letter punch – individualNormal script A – Z Character
height / Characters 6/H mm

085431 6/H

Letter punch – individualNormal script A – Z Character
height / Characters 6/L mm

085431 6/L

Letter punch – individualNormal script A – Z Character
height / Characters 6/D mm

085431 6/D

Letter punch – individualNormal script A – Z Character
height / Characters 6/Z mm

085431 6/Z

Letter punch – individualNormal script A – Z Character
height / Characters 6/B mm

085431 6/B

Letter punch – individualNormal script A – Z Character
height / Characters 6/Q mm

085431 6/Q

Letter punch – individualNormal script A – Z Character
height / Characters 6/G mm

085431 6/G

Letter punch – individualNormal script A – Z Character
height / Characters 6/P mm

085431 6/P

Letter punch – individualNormal script A – Z Character
height / Characters 6/C mm

085431 6/C