

Mitutoyo**Vernier caliper, Measuring range: 200mm****Order data**

Order number	412101 200
GTIN	4946368110189
Item class	44A

Description**Version:**

Satin chromium plated anti-glare scales.

Fine, high-contrast scale.

Locking screw at the top.

Precision ground measuring faces.

Optional extras:

Thread table No. 412180 for caliper back.

Technical description

Graduation	1/128 in
Calibration	A1
Graduation	1/20 mm
Scale divisions	0.05 mm
Measuring range	200 mm
Jaw length	50 mm
Reversible reading	mm / inch
Packaging	Wallet
Length of cross tips	20.5 mm
Standard	ISO 13385
Weight	180 g

Depth gauge	rectangular 3.7×1.4
Depth gauge available	yes
Measurement deviation E MPE	± 0.05 mm
Scale chrome plated	yes
Locking	Locking screw at top
Guidance	Raised slides
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Depth gauge holder, metal with 2 screws	412120
---	--------