


Mitutoyo**Digital caliper IP67, Measuring range: 200mm****Order data**

Order number	412623 200
GTIN	4946368693989
Item class	44A

Description**Version:**

Electronic caliper with absolute electronics and large easy-to-read display. Resistant to water, oil, and dust. Low energy consumption permits 18000 h continuous use on a single battery (size 300: 5000 h). The device is turned on automatically when it is moved and switches off automatically when not used for about 20 minutes.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357.

Technical description

Depth gauge	rectangular 3.7×1.4
Measuring range	0 - 200 mm
Calibration	A1
Standard	ISO 13385
Depth gauge available	yes
Scale divisions	0.01 mm
Auto switch-off	yes
Working time	15000 h
Jaw length	50 mm

Measured value saving	Once-off setting of the zero position
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 357
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	± 0.02 mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200
CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Button cell / special battery Battery type 357	081560 357
Depth gauge holder, metal with 2 screws	412120