

Mitutoyo**Digital caliper IP67 with data output, Measuring range: 150mm****Order data**

Order number	412628 150
GTIN	4946368693941
Item class	44A

Description**Version:**

Electronic caliper with absolute electronics and large easy-to-read display. Resistant to water, oil, and dust. Low energy consumption permits 18000 h continuous use on a single battery (size 300: 5000 h). The device is turned on automatically when it is moved and switches off automatically when not used for about 20 minutes.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Connecting cable (screw-on) No. 497085.

Technical description

Measuring range	0 - 150 mm
Depth gauge	rectangular 3.7×1.4
Auto switch-off	yes
Scale divisions	0.01 mm
Jaw length	40 mm
Depth gauge available	yes
Working time	15000 h

Calibration	A1
Standard	ISO 13385
Measured value saving	Once-off setting of the zero position
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	± 0.02 mm
Interface	Digimatic interface
Interface	USB interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Receiver / USB keyboard interface Type	498965
Connecting cablewith data switch Type D2	497085 D2
Connecting cablewith data switch Type D1	497085 D1
Multi-receiver / USB keyboard interface Type	498975
Connecting cablewith data switch Type USB2	497085 USB2
Transmitter Type S11E	498966 S11E

Button cell / special battery Battery type 357	081560 357
Depth gauge holder, metal with 2 screws	412120