

Mitutoyo**Digital caliper IP67 with data output, Measuring range: 200mm****Order data**

Order number	412628 200
GTIN	4946368694009
Item class	44A

Description**Version:**

Electronic caliper with absolute electronics and large easy-to-read display. Resistant to water, oil, and dust. Low energy consumption permits 18000 h continuous use on a single battery (size 300: 5000 h). The device is turned on automatically when it is moved and switches off automatically when not used for about 20 minutes.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Connecting cable (screw-on) No. 497085.

Technical description

Standard	ISO 13385
Working time	15000 h
Measuring range	0 - 200 mm
Jaw length	50 mm
Auto switch-off	yes
Scale divisions	0.01 mm
Depth gauge available	yes

Depth gauge	rectangular 3.7×1.4
Calibration	A1
Measured value saving	Once-off setting of the zero position
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081560 357
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	±0.02 mm
Interface	Digimatic interface
Interface	USB interface
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200
CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200

Accessories

Connecting cablewith data switch Type USB2	497085 USB2
Connecting cablewith data switch Type D2	497085 D2
Depth gauge holder, metal with 2 screws	412120
Connecting cablewith data switch Type D1	497085 D1
Button cell / special battery Battery type 357	081560 357
Receiver / USB keyboard interface Type	498965

Transmitter Type S11E	498966 S11E
Multi-receiver / USB keyboard interface Type	498975