

**Mitutoyo****Digital caliper IP67 with rod type depth gauge, Measuring range: 150mm****Order data**

Order number	412624 150
GTIN	4946368694030
Item class	44A

**Description****Version:**

Electronic caliper with absolute electronics and large easy-to-read display. Resistant to water, oil, and dust. Low energy consumption permits 18000 h continuous use on a single battery (size 300: 5000 h). The device is turned on automatically when it is moved and switches off automatically when not used for about 20 minutes.

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

1 battery No. 081560 size 357.

**Technical description**

Depth gauge available	yes
Calibration	A1
Jaw length	40 mm
Standard	ISO 13385
Auto switch-off	yes
Scale divisions	0.01 mm
Measuring range	0 - 150 mm
Working time	15000 h
Depth gauge	Ø 1.9

Measured value saving	Once-off setting of the zero position
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
IP Index of Protection	IP 67
Power supply	Battery-powered
Measurement deviation E MPE	$\pm 0.02$ mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

## Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

## Accessories

Button cell / special battery Battery type 357	081560 357
Depth gauge holder, metal with 2 screws	412120