



Angle grinder, Type: 72217360



Order data

Order number	077102 72217360
GTIN	4014586875033
Item class	03F

Description

Version:

Light-weight and powerful **115 mm one-hand angle grinder** in **handy compact design**, drive head can be rotated in 90° steps, quick adjustment of protective cover, M14 grinding spindle thread.

Sturdy **800 W** motor, all-metal drive head, spindle locking, restart inhibit.

Supplied with:

Supplied with protective hood, clamping set and additional handle.

Manufacturer's designation: WSG 8-115

Power consumption: 800 W

Speed range: 11000 min⁻¹

maximum disc Ø: 115 mm

maximum cutting depth: 34 mm

Weight: 2 kg

Technical description

Power consumption	800 W
Weight	2 kg
maximum disc Ø	115 mm
Manufacturer's designation	WSG 8-115

maximum cutting depth	34 mm
Restart block	yes
maximum vibration to EN	5 m/s ²
Speed range	11000 min ⁻¹
Power supply	Mains operated
Type of product	Angle grinder