



## Angle grinder, Type: AG10-115EK



### Order data

Order number	077103 AG10-115EK
GTIN	4002395260867
Item class	03M

### Description

#### Version:

Light-weight and powerful **115 mm one-hand angle grinder** in **handy compact design**, drive head can be rotated in 90° steps, quick adjustment of protective cover, M14 grinding spindle thread.

**1000 W** motor, spindle locking, restart inhibit.

#### Supplied with:

Supplied with protective hood, clamping set and additional handle.

### Technical description

Power consumption	1000 W
maximum vibration to EN	8.3 m/s <sup>2</sup>
Manufacturer's designation	AG10-115EK
Weight	2.1 kg
Restart block	yes
maximum cutting depth	28 mm
maximum disc Ø	115 mm
Speed range	11000 min <sup>-1</sup>
Power supply	Mains operated
Type of product	Angle grinder

