



Angle grinder GWS, Type: 7-125



Order data

Order number	077109 7-125
GTIN	3165140823715
Item class	03C

Description

Version:

Handy compact angle grinder with narrow handle circumference.

- **720 Watt motor and only 1.9 kg weight, optimised air inlets (direct cooling) for longer working life, restart inhibit.**
- **Very small handle circumference (176 mm) compared to other angle grinders in its wattage class, flat gearbox head permits use in inaccessible places.**

Supplied with:

Supplied with torsion-resistant protective hood, clamping set, additional handle.

Technical description

Power consumption	720 W
Manufacturer's designation	GWS 7-125
Special features	Narrow handle circumference
maximum vibration to EN	6.5 m/s ²
Restart block	yes
Weight	1.9 kg
maximum disc Ø	125 mm
maximum cutting depth	34 mm

Speed range	11000 min ⁻¹
Power supply	Mains operated
Type of product	Angle grinder