



Angle grinder GWS, Type: 13-125CI



Order data

Order number	077109 13-125CI
GTIN	3165140820134
Item class	03C

Description

Version:

Powerful angle grinder in a compact format.

- **Powerful motor with constant-speed electronics, soft start and start-up current limitation.**
- **Long working life, thanks to direct cooling and overload protection.**
- **High user protection due to vibration control. Additional handle, kick-back stop and restart inhibit.**

1300 W motor.

Supplied with:

Supplied with torsion-resistant protective hood, clamping set, additional handle.

Manufacturer's designation: GWS 13-125 CI

Power consumption: 1300 W

Speed range: 11500 min⁻¹

maximum disc Ø: 125 mm

maximum cutting depth: 34 mm

Weight: 2.3 kg

Technical description

Manufacturer's designation	GWS 13-125 CI
Special features	Compact design

Data sheet

Kick-back stop	yes
Restart block	yes
maximum cutting depth	34 mm
maximum vibration to EN	6 m/s ²
Power consumption	1300 W
Weight	2.3 kg
maximum disc Ø	125 mm
Speed range	11500 min ⁻¹
Power supply	Mains operated
Type of product	Angle grinder