



Angle grinder GWS, Type: 19-125CI



Order data

Order number	077109 19-125CI
GTIN	3165140838375
Item class	03C

Description

Version:

Very powerful 1900 W angle grinder for maximum productivity and very good user protection

- Long working life due to motors with direct motor cooling, constant-speed electronics, overload protection and long-life carbon brushes.
- Easy to use due to slim body with Softgrip surface for a secure grip.
- Additional handle for 40 % reduction in vibration, ensuring non-fatiguing working (EN 60745).
- Top user protection due to kick-back stop, restart inhibit, torsion-resistant protective hood and reduced vibration.

Supplied with:

Supplied with torsion-resistant protective hood, clamping set, additional handle.

Technical description

Power consumption	1900 W
maximum vibration to EN	6 m/s ²
Manufacturer's designation	GWS 19-125 CI
Kick-back stop	yes
maximum cutting depth	34 mm

maximum disc Ø	125 mm
Restart block	yes
Special features	Maximum power
Weight	2.4 kg
Speed range	11500 min ⁻¹
Power supply	Mains operated
Type of product	Angle grinder