



Compact angle grinder, Type: 722213



Order data

Order number	077111 722213
GTIN	4014586883496
Item class	03F

Description

Version:

FEIN – Compact angle grinder Ø 125 mm.

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

With variable speed, ideal for grinding stainless steel.

Supplied with:

Handle, safety guard, clamping nut, wrench.
Manufacturer's designation: WSG 17-70 INOX
Power consumption: 1700 W
maximum speed: 2700 – 8500 min⁻¹
maximum disc Ø: 125 mm
maximum cutting depth: 31 mm
Weight: 2.4 kg

Technical description

Dead man's circuit	no
Restart block	yes
Weight	2.4 kg
maximum speed	2700 – 8500 min ⁻¹
Power consumption	1700 W
maximum vibration to EN	5 m/s ²
Special features	variable speed
maximum disc Ø	125 mm
maximum cutting depth	31 mm
Manufacturer's designation	WSG 17-70 INOX
Power supply	Mains operated
Type of product	Angle grinder