

AEG

Compact angle grinder, Type: WS10-125S



Order data

Order number	077121 WS10-125S
GTIN	4002395151202
Item class	07A

Description

Version:

AEG – Compact angle grinder Ø 125 mm. Powerful and ergonomic **angle grinder** in compact slim design.

- **Safety spindle lock.**
- **Power cable 4 m.**
- **Dustproof bearings and switch.**
- **Grinding head can be rotated in steps of 90° for left-hand and right-handed use.**
- **Restart inhibit.**

Single-hand operation angle grinder 1000 W / Ø 125 mm.

Supplied with:

Handle, safety guard, clamping nut.

Note:

All compact angle grinders with lockable switch have no dead man's switch.

Technical description

Power consumption	1000 W
Weight	2.4 kg
maximum cutting depth	32 mm
Dead man's circuit	no

maximum disc Ø	125 mm
Restart block	yes
maximum vibration to EN	6 m/s ²
Manufacturer's designation	WS10-125S
Special features	M14
Power supply	Mains operated
maximum speed	11500 min ⁻¹
Type of product	Angle grinder

Accessories

Detachable protective guard for WS-125 Type GUARD-125	077122 GUARD-125
---	------------------