

# AEG

## Compact angle grinder, Type: WS13125SXE



### Order data

Order number	077121 WS13125SXE
GTIN	4002395151271
Item class	07A

### Description

#### Version:

**AEG – Compact angle grinder Ø 125 mm.** Powerful and ergonomic **angle grinder** in compact slim design.

- **Safety spindle lock.**
- **Power cable 4 m.**
- **Dustproof bearings and switch.**
- **Grinding head can be rotated in steps of 90° for left-hand and right-handed use.**
- **Restart inhibit.**

One-handed angle grinder 1300 W / Ø 125 mm, constant-speed electronics with no-load speed limitation and overload protection. **FIXTEC** clamping nut.

#### Supplied with:

Handle, safety guard, clamping nut.

#### Note:

All compact angle grinders with lockable switch have no dead man's switch.

### Technical description

maximum vibration to EN	7.5 m/s <sup>2</sup>
Weight	2.4 kg
maximum disc Ø	125 mm

Special features	M14, FIXTEC
maximum cutting depth	32 mm
Manufacturer's designation	WS13125SXE
Restart block	yes
Dead man's circuit	no
Power consumption	1300 W
Power supply	Mains operated
maximum speed	2600 - 11000 min <sup>-1</sup>
Type of product	Angle grinder

---

## Accessories

Detachable protective guard for WS-125 Type GUARD-125	077122 GUARD-125
---	------------------