



Angle grinder, Type: 7222196



Order data

Order number	077138 7222196
GTIN	4014586883618
Item class	03F

Description

Version:

FEIN ErgoGrip angle grinder with ergonomically shaped handler, for non-fatiguing working and low applied force. Optimum grip, even when wearing welders' gloves. Also suitable for working overhead. Powerful motor for high removal rate with low vibration. **Dead man's switch with restart inhibit**, requires both hands on the grinder.

Supplied with:

Supplied with protective hood, 1 pair of flanges, anti-vibration handle, wrench.

Manufacturer's designation: WSG17-125PRT

Power consumption: 1700 W

maximum speed: 11,000 min⁻¹

maximum disc Ø: 125 mm

maximum cutting depth: 33 mm

Weight: 2.4 kg

Technical description

Dead man's circuit	yes
maximum vibration to EN	2.1 m/s ²
Weight	2.4 kg
maximum cutting depth	33 mm
Restart block	yes

maximum speed	11,000 min ⁻¹
Manufacturer's designation	WSG17-125PRT
Power consumption	1700 W
maximum disc Ø	125 mm
Power supply	Mains operated
Type of product	Angle grinder