



Angle grinder GWS, Type: 24-230JVX



Order data

Order number	077153 24-230JVX
GTIN	3165140601795
Item class	03C

Description

Version:

Powerful 230 mm angle grinder:

- **Powerful motor with constant-speed electronics, smooth start-up and inrush current limitation.**
- **High protection of the user by vibration control on the main and auxiliary handles, kick-back stop and restart inhibit.**
- **Adjustable grasp handle for optimum grinding and cutting.**
- **SDS quick-clamping nut and spindle lock.**

2400 W motor and additional **run-out brake**.

Supplied with:

Supplied with protective hood, additional handle.

With SDS quick-clamping nut.

Manufacturer's designation: GWS 24-230 JVX

Power consumption: 2400 W

maximum speed: 6,500 min⁻¹

maximum disc Ø: 230 mm

maximum cutting depth: 69 mm

Weight: 6.5 kg

Technical description

maximum cutting depth	69 mm
Soft start	yes

maximum speed	6,500 min ⁻¹
Power consumption	2400 W
Restart block	yes
Weight	6.5 kg
Special features	Constant-speed electronics, run-out brake
Manufacturer's designation	GWS 24-230 JVX
maximum vibration to EN	6.5 m/s ²
maximum disc Ø	230 mm
Kick-back stop	yes
Power supply	Mains operated
Type of product	Angle grinder