

**FLEX**

## Pipework linisher, Type: SET



### Order data

|              |               |
|--------------|---------------|
| Order number | 077761 SET    |
| GTIN         | 4030293187191 |
| Item class   | 03S           |

### Description

#### Version:

Powerful pipework linisher with speed pre-selection, constant-speed electronics with tacho generator, soft start, **restart inhibit**, overload protection and temperature monitoring. With quick-release coupling for changing the modular attachments for burnishing and pipe linishing **without tools**. Electronics module completely encapsulated, thereby preventing damage by ingress of dust. High-quality spring-mounted linishing arm with 2 diverter rollers for optimum wrapping around pipes up to 270°.

#### Supplied with:

1 pipework linisher BRE14-3 125SET, 1 linishing belt attachment BR125, 1 pc. each super-finishing belt S600, S1500, 1 pc. each linishing belt Meshflex A240, A400, 5 pcs. each linishing belts Coruflex P80, P120, P220, 1 carrying case L-BOXX® 238.

#### Note:

For linishing belts see from No. 558408 onwards.

Packaging: Carrying case

Manufacturer's designation: BRE14-3 125SET

Power consumption: 1400 W

Tape width: 40 mm

Band length: 760 mm

pipework Ø for linishing: 125 mm

Weight: 3.6 kg

### Technical description

|                            |                    |
|----------------------------|--------------------|
| Manufacturer's designation | BRE14-3 125SET     |
| maximum belt speed         | 10 mm/s            |
| Weight                     | 3.6 kg             |
| Tape width                 | 40 mm              |
| Power consumption          | 1400 W             |
| pipework Ø for linishing   | 125 mm             |
| maximum vibration to EN    | 0 m/s <sup>2</sup> |
| Band length                | 760 mm             |
| Type                       | SET                |
| Power supply               | Mains operated     |
| Packaging                  | Carrying case      |
| Type of product            | Pipework linishers |

## Accessories

|   |            |
|---|------------|
| Linishing belt ceramic grit XK870T Grit 60  | 558398 60  |
| Linishing belt ceramic grit XK870X Grit 60  | 558410 60  |
| Linishing belt ceramic grit XK870X Grit 120 | 558410 120 |
| Linishing belt ceramic grit XK870T Grit 80  | 558401 80  |
| Linishing belt ceramic grit XK870X Grit 40  | 558409 40  |
| Linishing belt ceramic grit XK870T Grit 40  | 558402 40  |
| Linishing belt ceramic grit XK870T Grit 60  | 558407 60  |
| Linishing belt ceramic grit XK870T Grit 60  | 558404 60  |
| Linishing belt ceramic grit XK870F Grit 60  | 558411 60  |
| Linishing belt ceramic grit XK870X Grit 60  | 558409 60  |
| Linishing belt ceramic grit XK870X Grit 40  | 558430 40  |
| Linishing belt ceramic grit XK870T Grit 120 | 558399 120 |
| Linishing belt ceramic grit XK870T Grit 40  | 558397 40  |
| Linishing belt ceramic grit XK870F Grit 120 | 558408 120 |

|   |            |
|---|------------|
| Linishing belt ceramic grit XK870T Grit 80  | 558404 80  |
| Linishing belt ceramic grit XK870X Grit 80  | 558430 80  |
| Linishing belt ceramic grit XK870T Grit 120 | 558404 120 |
| Linishing belt ceramic grit XK870T Grit 40  | 558412 40  |
| Linishing belt ceramic grit XK870X Grit 60  | 558430 60  |
| Linishing belt ceramic grit XK870T Grit 40  | 558398 40  |
| Linishing belt ceramic grit XK870T Grit 40  | 558407 40  |
| Linishing belt ceramic grit XK870X Grit 120 | 558430 120 |
| Linishing belt ceramic grit XK870T Grit 120 | 558397 120 |
| Linishing belt ceramic grit XK870X Grit 24  | 558410 24  |
| Linishing belt ceramic grit XK870T Grit 60  | 558401 60  |
| Linishing belt ceramic grit XK870T Grit 120 | 558407 120 |
| Linishing belt ceramic grit XK870T Grit 60  | 558399 60  |
| Linishing belt ceramic grit XK870T Grit 120 | 558414 120 |
| Linishing belt ceramic grit XK870X Grit 24  | 558430 24  |
| Linishing belt ceramic grit XK870F Grit 120 | 558411 120 |
| Linishing belt ceramic grit XK870T Grit 40  | 558414 40  |
| Linishing belt ceramic grit XK870T Grit 80  | 558399 80  |
| Linishing belt ceramic grit XK870T Grit 80  | 558414 80  |
| Linishing belt ceramic grit XK870X Grit 36  | 558409 36  |
| Linishing belt ceramic grit XK870T Grit 120 | 558401 120 |
| Linishing belt ceramic grit XK870T Grit 60  | 558414 60  |
| Linishing belt ceramic grit XK870T Grit 80  | 558398 80  |
| Linishing belt ceramic grit XK870X Grit 40  | 558410 40  |
| Linishing belt ceramic grit XK870X Grit 120 | 558409 120 |
| Linishing belt ceramic grit XK870T Grit 120 | 558402 120 |
| Linishing belt ceramic grit XK870T Grit 40  | 558404 40  |
| Linishing belt ceramic grit XK870F Grit 60  | 558408 60  |
| Linishing belt ceramic grit XK870T Grit 80  | 558407 80  |

|   |            |
|---|------------|
| Linishing belt ceramic grit XK870X Grit 80  | 558409 80  |
| Linishing belt ceramic grit XK870F Grit 80  | 558408 80  |
| Linishing belt ceramic grit XK870T Grit 80  | 558412 80  |
| Linishing belt ceramic grit XK870X Grit 36  | 558430 36  |
| Linishing belt ceramic grit XK870T Grit 40  | 558399 40  |
| Linishing belt ceramic grit XK870T Grit 60  | 558412 60  |
| Linishing belt ceramic grit XK870T Grit 60  | 558397 60  |
| Linishing belt ceramic grit XK870X Grit 36  | 558410 36  |
| Linishing belt ceramic grit XK870F Grit 80  | 558411 80  |
| Linishing belt ceramic grit XK870T Grit 80  | 558402 80  |
| Linishing belt ceramic grit XK870T Grit 120 | 558412 120 |
| Linishing belt ceramic grit XK870X Grit 80  | 558410 80  |
| Linishing belt ceramic grit XK870T Grit 40  | 558401 40  |
| Linishing belt ceramic grit XK870T Grit 80  | 558397 80  |
| Linishing belt ceramic grit XK870T Grit 120 | 558398 120 |
| Linishing belt ceramic grit XK870T Grit 60  | 558402 60  |