

FLEX

Pipework linisher, Type: SET



Order data

Order number	077761 SET
GTIN	4030293187191
Item class	03S

Description

Version:

Powerful pipework linisher with speed pre-selection, constant-speed electronics with tacho generator, soft start, **restart inhibit**, overload protection and temperature monitoring. With quick-release coupling for changing the modular attachments for burnishing and pipe linishing **without tools**. Electronics module completely encapsulated, thereby preventing damage by ingress of dust. High-quality spring-mounted linishing arm with 2 diverter rollers for optimum wrapping around pipes up to 270°.

Supplied with:

1 pipework linisher BRE14-3 125SET, 1 linishing belt attachment BR125, 1 pc. each super-finishing belt S600, S1500, 1 pc. each linishing belt Meshflex A240, A400, 5 pcs. each linishing belts Coruflex P80, P120, P220, 1 carrying case L-BOXX® 238.

Note:

For linishing belts see from No. 558408 onwards.

Packaging: Modular case (L-Boxx)

Manufacturer's designation: BRE14-3 125SET

Power consumption: 1400 W

Tape width: 40 mm

Band length: 760 mm

pipework Ø for linishing: 125 mm

Weight: 3.6 kg

Technical description

Manufacturer's designation	BRE14-3 125SET
maximum belt speed	10 mm/s
Weight	3.6 kg
Tape width	40 mm
Power consumption	1400 W
pipework Ø for linishing	125 mm
maximum vibration to EN	0 m/s ²
Band length	760 mm
Type	SET
Power supply	Mains operated
Packaging	Modular case (L-Boxx)
Type of product	Pipework linishers

Accessories

Linishing belt ceramic grit XK870T Grit 60	558398 60
Linishing belt ceramic grit XK870X Grit 60	558410 60
Linishing belt ceramic grit XK870X Grit 120	558410 120
Linishing belt ceramic grit XK870T Grit 80	558401 80
Linishing belt ceramic grit XK870X Grit 40	558409 40
Linishing belt ceramic grit XK870T Grit 40	558402 40
Linishing belt ceramic grit XK870T Grit 60	558407 60
Linishing belt ceramic grit XK870T Grit 60	558404 60
Linishing belt ceramic grit XK870F Grit 60	558411 60
Linishing belt ceramic grit XK870X Grit 60	558409 60
Linishing belt ceramic grit XK870X Grit 40	558430 40
Linishing belt ceramic grit XK870T Grit 120	558399 120
Linishing belt ceramic grit XK870T Grit 40	558397 40
Linishing belt ceramic grit XK870F Grit 120	558408 120

Linishing belt ceramic grit XK870T Grit 80	558404 80
Linishing belt ceramic grit XK870X Grit 80	558430 80
Linishing belt ceramic grit XK870T Grit 120	558404 120
Linishing belt ceramic grit XK870T Grit 40	558412 40
Linishing belt ceramic grit XK870X Grit 60	558430 60
Linishing belt ceramic grit XK870T Grit 40	558398 40
Linishing belt ceramic grit XK870T Grit 40	558407 40
Linishing belt ceramic grit XK870X Grit 120	558430 120
Linishing belt ceramic grit XK870T Grit 120	558397 120
Linishing belt ceramic grit XK870X Grit 24	558410 24
Linishing belt ceramic grit XK870T Grit 60	558401 60
Linishing belt ceramic grit XK870T Grit 120	558407 120
Linishing belt ceramic grit XK870T Grit 60	558399 60
Linishing belt ceramic grit XK870T Grit 120	558414 120
Linishing belt ceramic grit XK870X Grit 24	558430 24
Linishing belt ceramic grit XK870F Grit 120	558411 120
Linishing belt ceramic grit XK870T Grit 40	558414 40
Linishing belt ceramic grit XK870T Grit 80	558399 80
Linishing belt ceramic grit XK870T Grit 80	558414 80
Linishing belt ceramic grit XK870X Grit 36	558409 36
Linishing belt ceramic grit XK870T Grit 120	558401 120
Linishing belt ceramic grit XK870T Grit 60	558414 60
Linishing belt ceramic grit XK870T Grit 80	558398 80
Linishing belt ceramic grit XK870X Grit 40	558410 40
Linishing belt ceramic grit XK870X Grit 120	558409 120
Linishing belt ceramic grit XK870T Grit 120	558402 120
Linishing belt ceramic grit XK870T Grit 40	558404 40
Linishing belt ceramic grit XK870F Grit 60	558408 60
Linishing belt ceramic grit XK870T Grit 80	558407 80

Linishing belt ceramic grit XK870X Grit 80	558409 80
Linishing belt ceramic grit XK870F Grit 80	558408 80
Linishing belt ceramic grit XK870T Grit 80	558412 80
Linishing belt ceramic grit XK870X Grit 36	558430 36
Linishing belt ceramic grit XK870T Grit 40	558399 40
Linishing belt ceramic grit XK870T Grit 60	558412 60
Linishing belt ceramic grit XK870T Grit 60	558397 60
Linishing belt ceramic grit XK870X Grit 36	558410 36
Linishing belt ceramic grit XK870F Grit 80	558411 80
Linishing belt ceramic grit XK870T Grit 80	558402 80
Linishing belt ceramic grit XK870T Grit 120	558412 120
Linishing belt ceramic grit XK870X Grit 80	558410 80
Linishing belt ceramic grit XK870T Grit 40	558401 40
Linishing belt ceramic grit XK870T Grit 80	558397 80
Linishing belt ceramic grit XK870T Grit 120	558398 120
Linishing belt ceramic grit XK870T Grit 60	558402 60