

FLEX
TRINOX FLEX burnishing machine, Type: BSE14-3

Order data

Order number	077751 BSE14-3
GTIN	4030293187177
Item class	03S

Description
Version:

Powerful TRINOFLEX BSE 14-3 100 burnishing machine with constant-speed electronics.

- **Speed pre-selection and stability by means of a tacho generator.**
- **Soft start, overload protection and restart inhibit after a power failure.**
- **Electronics module completely encapsulated, thereby preventing damage by ingress of dust.**

Application:

For burnishing, polishing, brushing, smoothing, rust removal and deburring.

Supplied with:

Burnishing machine BSE14-3 100, 1 burnishing attachment BS100.

Manufacturer's designation: BSE 14-3 100

Power consumption: 1400 W

Speed range: 1000 - 3500 min⁻¹

Toolholder: 19

Polishing tool length: 100 mm

maximum polishing tool Ø: 125 mm

Technical description

Toolholder	19
Manufacturer's designation	BSE 14-3 100
Speed range	1000 - 3500 min ⁻¹

maximum vibration to EN	0 m/s ²
Polishing tool length	100 mm
Power consumption	1400 W
maximum polishing tool Ø	125 mm
Weight	2.9 kg
Power supply	Mains operated
Type of product	Burnishing machine

Accessories

Mini-linishing belt Ø 100×100 mm Grit 180	568538 180
Mini-linishing belt Ø 100×100 mm Grit 120	568538 120
Backing roller Ø 100×100 mm Type AIR	568577 AIR
Mini-linishing belt Ø 100×100 mm Grit 280	568535 280
Mini-linishing belt Ø 100×100 mm Grit equivalent 280	568558 280
Mini-linishing belt Ø 100×100 mm Grit 80	568535 80
Mini-linishing belt Ø 100×100 mm Grit equivalent 180	568558 180
Mini-linishing belt Ø 100×100 mm Grit 240	568538 240
Mini-linishing belt Ø 100×100 mm Grit 120	568532 120
Mini-linishing belt Ø 100×100 mm Grit 40	568532 40
Mini-linishing belt Ø 100×100 mm Grit 280	568538 280
Mini-linishing belt Ø 100×100 mm Grit 600	568538 600
Mini-linishing belt Ø 100×100 mm Grit 80	568532 80
Mini-linishing belt Ø 100×100 mm Grit equivalent 100	568558 100
Mini-linishing belt Ø 100×100 mm Grit 120	568535 120
Mini-linishing belt Ø 100×100 mm Grit 60	568532 60