



Deburring and chamfering machine, Type: EKF452



Order data

Order number	078121 EKF452
GTIN	4250187507267
Item class	07E

Description

Version:

Chamfering machine with smooth start-up and thermal overload protection for machining straight edges, internal and external radii and holes from 22 mm Ø. Fine adjustment permits light chamfering for deburring and also wide chamfering. With improved cutter head for reduced cutting forces. Radius R 2.5 mm.

Supplied with:

Milling head, **3 carbide** inserts, swarf hook No. 084520 and transport case.

Note:

A component edge height of at least 2 mm is necessary to provide guidance.

Technical description

AC supply voltage	230 V
Power consumption	1500 W
Length	310 mm
Manufacturer's designation	EKF452

Width	138 mm
maximum speed	6000 min ⁻¹
Weight	4 kg
Height	295 mm
Radius	2.5 mm
Power supply	Mains operated
Packaging	Carrying case
Type of product	Deburring and chamfering machine

Accessories

Carbide insert set, 3 pieces, SHM 202for steel radius 2.5 mm Type SHM202	078131 SHM202
Spare screw for EKF inserts Version SCREW	078127 SCREW
Milling tool3-cutter Type ZFR452	078133 ZFR452