

**GSS orbital sander, Type: 230AVE****Order data**

Order number	077328 230AVE
GTIN	3165140663779
Item class	03C

Description**Version:**

Handy low-vibration 300 W orbital sander with speed pre-selection:

- **Ergonomically shaped holding surfaces with softgrip permit perfect handling.**
- **Very low vibration thanks to decoupling of the motor casing.**
- **Precise seating of abrasive paper sheets, be they clamp fitting or hook and loop fastener fitting.**
- **Integral dust extraction through 8-hole abrasive paper.**
- **Direct connection to micro-filter box or external dust extraction system.**

Supplied with:

Supplied with micro-filter box, abrasive plate, additional handle.

Note:

For a suitable hook and loop fastener sanding paper see No. 557576.

Power consumption: 300 W

Abrasive paper length (hook and loop): 184 mm

Abrasive paper width (hook and loop): 92 mm

Abrasive paper length (clamped): 230 mm

Abrasive paper width (clamped): 92 mm

Orbital stroke: 2.4 mm

Technical description

Abrasive paper width (hook and loop)	92 mm
--------------------------------------	-------

Abrasive paper width (clamped)	92 mm
Manufacturer's designation	230AVE
Hole pattern	8-hole
Abrasive paper length (hook and loop)	184 mm
Abrasive paper mounting clamped	yes
maximum vibration to EN	$< 2.5 \text{ m/s}^2$
Power consumption	300 W
Speed of oscillation	22000 min^{-1}
Abrasive paper mounting hook and loop	yes
Weight	2.4 kg
Abrasive paper length (clamped)	230 mm
Orbital stroke	2.4 mm
Power supply	Mains-powered
Type of product	Orbital sander

Accessories

Abrasive paper pack, 50 pieces 8 holes Grit 120	557576 120
Abrasive paper pack, 50 pieces 8 holes Grit 60	557576 60
Abrasive paper pack, 50 pieces 8 holes Grit 180	557576 180
Abrasive paper pack, 50 pieces 8 holes Grit 40	557576 40
Abrasive paper pack, 50 pieces 8 holes Grit 320	557576 320
Abrasive paper pack, 50 pieces 8 holes Grit 400	557576 400
Abrasive paper pack, 50 pieces 8 holes Grit 100	557576 100
Abrasive paper pack, 50 pieces 8 holes Grit 80	557576 80
Abrasive paper pack, 50 pieces 8 holes Grit 240	557576 240