



Battery / mains radio, Type: M18JSR



Order data

Order number	073960 M18JSR
GTIN	4002395167753
Item class	03L

Description

Version:

Sturdy site radio, splash-proof (IP54) for mains and battery operation.

- **USB port for charging mobile devices.**
- **AUX input for connecting external audio playback devices.**
- **LCD digital clock with batteries.**
- **Operation with Milwaukee 18 volt batteries or with 220-240 volt AC voltage.**

High-performance audio system with AM / FM tuner.

- **Two speakers with passive membranes generate a loud and clear sound with rich bass.**
- **Digital tuner with 10 memory spaces.**
- **Robust design protects the radio against splashed water and dust on building sites.**
- **Compartment for secure storage of MP3 player.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Includes mains cable, 2 back-up batteries, AUX connection cable, without batteries.

Technical description

Interface	USB interface
-----------	---------------

Manufacturer's designation	M18JSR-0
Height	200 mm
Length	400 mm
Width	400 mm
Battery voltage	18 V
Weight	5 kg
Number of rechargeable batteries contained	0
IP Index of Protection	IP 54
Power supply	Rechargeable battery-powered
Power supply	Mains operated
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
Type of product	Radio

Accessories

Battery charger Type M1218C	073840 M1218C
Li-ion system M18B5 Battery type MB18	073816 MB18
Battery charger Type M1218FC	073840 M1218FC