



Hydraulic cordless hole punch with matrices, Type: M18HKP-SET



Order data

Order number	078252 M18HKP-SET
GTIN	4002395138920
Item class	03L

Description

Version:

FORCE LOGIC™ **hydraulic 60 kN cordless hole punch** punches holes up to Ø 100 mm in 3mm steel or 2.5 mm stainless steel.

- **With 3/4-16 UNF tapped hole on the device.**
- **Quick-change system with key-less tool change permits punches and matrices to be assembled separately from the tool.**
- **Compatible with commercially-available accessories.**
- **Easily aligned thanks to matrices with cross-hairs.**

Supplied with:

M12-18C charger, carrying case, 1 each pull screw 11.1 mm (7/16-20 UNF) and 19 mm (3/4-16 UNF), Quick-change system with key-less tool change, punches and matrices with UNF threads for hole sizes: M16, M20, M25, M32, M40.

Note:

Suitable sheet metal punches with metric threads No. 834000 ff. (not size 12.5) and the necessary draw bolts 834070 can be found in Product Group 83.

Technical description

maximum diameter	100 mm
Battery capacity	2 Ah
Manufacturer's designation	M18HKP-201CA
suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
max. punching depth in steel	3 mm
Weight	2.3 kg
Packaging	Carrying case
max. punching depth in stainless steel	2.5 mm
Battery voltage	18 V
Press force	60 kN
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	1
Power supply	Rechargeable battery-powered
Type of product	Hole punch

Accessories

Battery charger Type M1218FC	073840 M1218FC
Li-ion system M18B2 Battery type MB18	073827 MB18
Battery charger Type M1218C	073840 M1218C