



LED industrial head lamp, Manufacturer's designation: ISEO3



Order data

Order number	081477 ISEO3
GTIN	4029113560306
Item class	04B

Description

Version:

Powerful high-quality **industrial** LED head lamps.

- **Pivoting head and stepless focussing function.**
- **Exchangeable washable headband.**

Very lightweight head lamp, easy to operate, with three lighting modes and additional non-dazzle **red LED with flashing function**. Protected against jets of water under pressure, IP X6.

Note:

The manufacturer only provides its 24-month guarantee for "i series" products with online registration. At <https://www.ledlenser.com/de/produkte/service-garantie/> you can find information about the online registration process.

IP Index of Protection: IP X6

Manufacturer's designation: ISEO3

ATEX zone: no

Illumination: 15 - 100 lm

Working life: 10 - 40 h

Number of batteries contained: 3

Battery type: Micro, AAA

Technical description

Illumination range	30 - 100 m
Battery type	Micro, AAA
Illumination	15 - 100 lm

Advanced Focus System (AFS)	yes
Power supply	Battery-powered
Weight	105 g
Smart Light Technology (SLT)	yes
Including belt pocket	yes
Manufacturer's designation	ISEO3
Number of batteries contained	3
Working life	10 - 40 h
Head Ø	29 mm
Rapid Focus	yes
IP Index of Protection	IP X6
ATEX zone	no
chemical composition	Alkaline manganese
rechargeable	no
Dimmable lighting	no