



## LED industrial head lamp, Manufacturer's designation: ISEO5R



### Order data

Order number	081477 ISEO5R
GTIN	4029113560504
Item class	04B

### Description

#### Version:

Powerful high-quality **industrial** LED head lamps.

- **Pivoting head and stepless focussing function.**
- **Exchangeable washable headband.**

Very lightweight head lamp, easy to operate, with three lighting modes and additional non-dazzle **red LED with flashing function**. Protected against jets of water under pressure, IP X6. Rechargeable. With Li-ion battery and USB charger.

#### Note:

The manufacturer only provides its 24-month guarantee for "i series" products with online registration. At <https://www.ledlenser.com/de/produkte/service-garantie/> you can find information about the online registration process.

IP Index of Protection: IP X6

Manufacturer's designation: ISEO5R

ATEX zone: no

Illumination: 20 - 180 lm

Working life: 5 - 20 h

Number of rechargeable batteries contained: 1

Type of rechargeable battery: Lithium-ion

### Technical description

Illumination	20 - 180 lm
Including belt pocket	yes
Advanced Focus System (AFS)	yes

Weight	93 g
Battery capacity	0.88 A·h
Battery voltage	3.7 V
Power supply	12
Working life	5 - 20 h
Illumination range	40 - 120 m
Manufacturer's designation	ISEO5R
Smart Light Technology (SLT)	yes
Head Ø	28 mm
Rapid Focus	yes
IP Index of Protection	IP X6
ATEX zone	no
Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Dimmable lighting	yes