

## HEDI

### Machine / workstation lamp, Type: 6LED



#### Order data

Order number	081300 6LED
GTIN	4003644000111
Item class	08B

#### Description

**Version:**

High quality, universally usable lamps for 250 V / 50 Hz with On / Off switch, 3 m rubber connection cable.

**Robust, long, coated flexible metal arm** for good mobility of the lamp head and high stability. Machine lamp with **LEDs** for directed illumination of the workplace. Low power consumption, avoids heating up the illuminated objects and subjecting them to UV radiation.

**Standard:**

High quality, universally usable lamps for 250 V / 50 Hz with On / Off switch, 3 m rubber connection cable.

- **Sturdy, long, coated flexible metal arm.**

**Supplied with:**

Bulb, with **strong magnetic clamp, 50 mm screw-on clamp, and mounting screws** for machine, table, wall or ceiling attachment.

**Attention:**

German version. Order free UK adapter plug No. 08 1172\_GB.

**Note:**

Available in warm white (3,000 K).

IP Index of Protection: IP 20

Light output: 6 W

Illumination: 450 lm

Number of LEDs: 4  
Connection cable length: 3 m  
Energy efficiency class : A

## Technical description

Number of LEDs	4
Illumination	450 lm
IP Index of Protection	IP 20
Power supply	Mains-powered
Connection cable length	3 m
Energy efficiency class	A
Light colour	6,500 K
Bulb	LED
Lamp replaceable	yes
Light output	6 W

## Accessories

Spare bulb suitable for type 6LED	081310 6LED
-----------------------------------	-------------