



Pneumatic drill, Type: D2116Q



Order data

Order number	079051 D2116Q
GTIN	7322590013288
Item class	03R

Description

Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø. A range of powerful and very smooth running drills with pistol grip and a drilling power of up to 13 mm in steel. Exhaust air is discharged through the handle, to prevent drill chips from swirling up. With quick-release chuck.

Supplied with:

Quick-clamping chuck.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

Quick-clamping chuck range	1.5 - 10 mm
Operating noise	82 dB(A)
maximum air consumption	600 l/min
Weight	1 kg
maximum speed	0 - 2400 min ⁻¹
Manufacturer's designation	D2116Q

recommended hose size (internal Ø)	10 mm
maximum vibration to EN	< 2.5 m/s ²
Length	211 mm
Output power	350 W
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Drill