



Socket set 1/2 inch square drive 23 pieces, Type: 12



Order data

Order number	637818 12
GTIN	4062406230838
Item class	62A

Description

Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120**. With bi-hexagon sockets No. 642120.

Application:

For hexagon head screws / nuts with thread M6 – M22.

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

Sockets: 17 pcs. size 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24; 27; 30; 32; 34 mm

T-handle: 1 pc. 641320

Extensions: 3 pcs. No. 641020 size 75; 130; 255

Universal joint: 1 pc. No. 641620

Ratchet: 1 pc. No. 640190

Storage in: ABS plastic box

Technical description

Width across flats	metric
Drive profile	Bi-hex socket
Square drive	1/2 in
Width across flats range, bi-hex sockets	10-34 mm

Number of pieces	23
Packaging	ABS plastic box
Length	407 mm
Width	227 mm
Height	62 mm
Type of product	Socket spanner

Accessories

Extension, 1/2 inch overall length 255 mm	641020 255
Reversible ratchet, 1/2 inch with ejector Type 1/2	640190 1/2
Universal joint, 1/2 inch Type 1/2	641620 1/2
Modular box Type 4	630323 4
Extension, 1/2 inch overall length 75 mm	641020 75
Rigid foam inlay for set 637818	630324 637818
Extension, 1/2 inch overall length 130 mm	641020 130
T-handle, 1/2 inch overall length 295 mm	641320 295