


**Garant**
**Centring vice basic device Xtric, Type: 125XSP**

**Order data**

Order number	363000 125XSP
GTIN	4062406229962
Item class	310

**Description**
**Version:**

- **Very good accessibility and perfectly symmetrical.**
- **Fully hardened and precision milled on the underside.**
- **Clamps raw materials and finished parts with the least possible backstroke of the jaws / component.**
- **Supplied with holes for LONG positioning system, can be adapted to GARANT ZeroClamp and Erowa ITS148 (size 50 and 80) using an intermediate plate.**
- **Jaws can be changed without using tools. The clamping range can be changed by reversing the jaws.**
- **Interface for automated applications.**
- **Easy-to-use, chuck jaw quick-change system, no tools required.**
- **Clamping force up to 25 kN at 90 Nm torque.**
- **Quick to use and intuitive in operation.**
- **Repetition accuracy <0.01 mm.**
- **Scaling for pre-positioning the clamping modules.**
- **Spindle nut with or without pivot function.**
- **Clamping lip for steplessly adjustable clamps.**
- **Centring adjustment with pin wrench.**

**Application:**

Perfect for 5-face machining. Centred clamping.

**Suitable for:**

Top jaws No. 363010 – 363045.

**Supplied with:**

Base rail, spindle, spindle nuts, **spindle cover No. 363083.**

**Optional extras:**

Hexagon screwdriver No. 627424 size 5, pin spanner No. 628600 size 2, torque wrench No. 656050, socket No. 642229, stepless adjustable clamps No. 363081 80 and 361165 CS1, GARANT clamping stud No. 363190, adapter plates No. 363079, 363080, 363085. Height extension base No. 363090 (in conjunction with No. 363079). Assembly station No. 358595 52/96.

**Note:**

Suitable top jaws No. 363010 – 363045 are not included in the scope of supply. Clamping situation S2 arises by reversing the jaws. Use offset top jaws to overcome the clamping gaps with types XS and XSP and H.

**Technical description**

Series	Xtric
B	125 mm
maximum torque	132 Nm
Clamping range S2	92 - 146 mm
Clamping range S1	0 - 60 mm
Height H	54 mm
Swing angle	±2 degrees
Weight	7.8 kg
Colour code for suitable accessories	Xtric 125
Width across flats	13 mm
Width across flats	5 mm
L	186 mm
Clamping force up to maximum	32 kN
Longitudinal slot	20 mm
Pitch underside	96 mm
Type of product	Machine vice

**Accessories**

Pair of parallelmagnetic Height 32 mm	363076 32
---------------------------------------	-----------

Pair of parallelmagnetic Height 30C mm	363076 30C
Adapter plate for centring vice ZS type / for clamping pot Ø 125/120 mm	363080 125/120
Pair of parallelmagnetic Height 25 mm	363076 25
Rigid right-hand spindle nut Type 125	363097 125
Spindle nut with right-hand pivot function Type 125	363099 125
Pair of parallelmagnetic Height 20 mm	363076 20
Pair of parallelmagnetic Height 10 mm	363076 10
Adapter plate for centring vice ZS type / for clamping pot Ø 125/138 mm	363080 125/138
Pair of parallelmagnetic Height 32C mm	363076 32C
Soft top jaw Type 160S	363034 160S
Soft top jaw Type 160A	363034 160A
Pair of parallelmagnetic Height 30 mm	363076 30
Spindle nut with left-hand pivot function Type 125	363098 125
Pair of parallelmagnetic Height 12 mm	363076 12