

PRYOR

Numeral letter punch set, 27 pieces Normal script A – Z, &, Character height: 10mm



Order data

Order number	085430 10
GTIN	5022044005181
Item class	08W

Description

Version:

Made of hard and tough steel with particularly precise machine engraving and depth tolerance; accurately centred. Calibrated shank, through hardened. Striking head enhancement for safe working. Supplied in a plastic case.

High performance precision punches, chemically nickel-plated, very long service life.

Normal script; i. e. the punched character can be read directly on the component.

Application:

For punching into materials with a **strength up to 1200 N/mm²**.

Spare part:

Individual number punches under No. 085411 size font height/number, e. g. No. 085411 size 3/1.

Individual letter punches under No. 085431 size font height/character, e.g. No. 085431 size 3/A.

Note:

Other hand and machine punches of all types, such as punches with a company's logo etc., are available on request.

Technical description

Character height	10 mm
overall length	89 mm

Shank thickness	14.3
Type of product	Hand punch

Accessories

Letter punch – individualNormal script A – Z Character height / Characters 10/T mm	085431 10/T
Letter punch – individualNormal script A – Z Character height / Characters 10/V mm	085431 10/V
Letter punch – individualNormal script A – Z Character height / Characters 10/L mm	085431 10/L
Letter punch – individualNormal script A – Z Character height / Characters 10/S mm	085431 10/S
Letter punch – individualNormal script A – Z Character height / Characters 10/R mm	085431 10/R
Letter punch – individualNormal script A – Z Character height / Characters 10/Z mm	085431 10/Z
Letter punch – individualNormal script A – Z Character height / Characters 10/U mm	085431 10/U
Letter punch – individualNormal script A – Z Character height / Characters 10/I mm	085431 10/I
Letter punch – individualNormal script A – Z Character height / Characters 10/B mm	085431 10/B
Letter punch – individualNormal script A – Z Character height / Characters 10/W mm	085431 10/W
Letter punch – individualNormal script A – Z Character height / Characters 10/N mm	085431 10/N
Letter punch – individualNormal script A – Z Character height / Characters 10/X mm	085431 10/X
Letter punch – individualNormal script A – Z Character height / Characters 10/G mm	085431 10/G
Letter punch – individualNormal script A – Z Character height / Characters 10/F mm	085431 10/F

Letter punch – individualNormal script A – Z Character height / Characters 10/J mm	085431 10/J
Letter punch – individualNormal script A – Z Character height / Characters 10/O mm	085431 10/O
Letter punch – individualNormal script A – Z Character height / Characters 10/P mm	085431 10/P
Letter punch – individualNormal script A – Z Character height / Characters 10/E mm	085431 10/E
Letter punch – individualNormal script A – Z Character height / Characters 10/D mm	085431 10/D
Punch holder Type GRIP	085475 GRIP
Letter punch – individualNormal script A – Z Character height / Characters 10/H mm	085431 10/H
Letter punch – individualNormal script A – Z Character height / Characters 10/A mm	085431 10/A
Letter punch – individualNormal script A – Z Character height / Characters 10/Y mm	085431 10/Y
Letter punch – individualNormal script A – Z Character height / Characters 10/M mm	085431 10/M
Letter punch – individualNormal script A – Z Character height / Characters 10/C mm	085431 10/C
Letter punch – individualNormal script A – Z Character height / Characters 10/& mm	085431 10/&
Letter punch – individualNormal script A – Z Character height / Characters 10/Q mm	085431 10/Q
Letter punch – individualNormal script A – Z Character height / Characters 10/K mm	085431 10/K