

**Garant**
**GARANT Master Mute boring bar shank vibration damping, 11×D, System / shank Ø: GL/16**

**Order data**

Order number	264870 GL/16
GTIN	4062406231415
Item class	29E

**Description**
**Version:**

Shank carbide reinforced.

**Supplied with:**

Reducing adaptor for coolant connection.

**Note:**

Do not clamp on the area marked S!

$D_{\min} = 1/2 \text{ shank } \varnothing + \text{ cutting head centre-line offset } L_3.$

Convenient boring bar orientation by set-up head No. 265001.

Through-coolant: yes

System: GL

Overall length L: 204 mm

non-clamping range S: 85 mm

recommended clamping length: 64 mm

Assembly bolt set: 269026 1

**Technical description**

non-clamping range S	85 mm
recommended clamping length	64 mm
System	GL
Assembly bolt set	269026 1
Overall length L	204 mm
suitable interchangeable cutting heads	264830; 264831

Series	Master Mute
Boring depth up to	11×D
Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks