

**Garant**
**GARANT Master Mute boring bar shank vibration damping, 11×D, System / shank Ø: DM/40**

**Order data**

Order number	264934 DM/40
GTIN	4062406231361
Item class	29E

**Description**
**Supplied with:**

Reducing adaptor for coolant connection.

**Note:**

Do not clamp on the area marked S!

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Convenient boring bar orientation by set-up head No. 265001.

Through-coolant: yes

System: DM

Overall length L: 528 mm

non-clamping range S: 196 mm

recommended clamping length: 160 mm

Assembly bolt set: 269026 3

**Technical description**

non-clamping range S	196 mm
recommended clamping length	160 mm
System	DM
Assembly bolt set	269026 3
High-pressure connecting hose	269207
Plug connector for coolant connection	269208
Overall length L	528 mm

suitable interchangeable cutting heads	264838; 264839
Series	Master Mute
Boring depth up to	11×D
Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks