

Garant
GARANT Master Mute boring bar shank vibration damping, 8×D, System / shank Ø: DM/40

Order data

Order number	264930 DM/40
GTIN	4062406231330
Item class	29E

Description
Supplied with:

Reducing adaptor for coolant connection.

Note:

Do not clamp on the area marked S!

$D_{\min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Convenient boring bar orientation by set-up head No. 265001.

Through-coolant: yes

System: DM

Overall length L: 408 mm

non-clamping range S: 144 mm

recommended clamping length: 160 mm

Assembly bolt set: 269026 3

Technical description

recommended clamping length	160 mm
non-clamping range S	144 mm
System	DM
Assembly bolt set	269026 3
High-pressure connecting hose	269207
Plug connector for coolant connection	269208
Overall length L	408 mm

suitable interchangeable cutting heads	264838; 264839
Series	Master Mute
Boring depth up to	8×D
Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks