

**Garant**
**GARANT Master Mute boring bar shank vibration damping, 8×D, System / shank Ø: QC/25**

**Order data**

Order number	264890 QC/25
GTIN	4062406231187
Item class	29E

**Description**
**Supplied with:**

Reducing adaptor for coolant connection.

**Note:**

Do not clamp on the area marked S!

$D_{min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Convenient boring bar orientation by set-up head No. 265001.

Through-coolant: yes

System: QC

Overall length L: 255 mm

Centre offset H base body: 2.5 mm

non-clamping range S: 107 mm

recommended clamping length: 100 mm

Assembly bolt set: 269026 1

**Technical description**

Centre offset H base body	2.5 mm
non-clamping range S	107 mm
recommended clamping length	100 mm
System	QC
Assembly bolt set	269026 1
Plug connector for coolant connection	269208
High-pressure connecting hose	269207

Overall length L	255 mm
suitable interchangeable cutting heads	264834; 264835
Series	Master Mute
Boring depth up to	8×D
Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks