

Garant
GARANT Master Mute boring bar shank vibration damping, 11×D, System / shank Ø: DM/60

Order data

Order number	264934 DM/60
GTIN	4062406231385
Item class	29E

Description
Supplied with:

Reducing adaptor for coolant connection.

Note:

Do not clamp on the area marked S!

$D_{\min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Convenient boring bar orientation by set-up head No. 265001.

Through-coolant: yes

System: DM

Overall length L: 808 mm

Centre offset H base body: 10 mm

non-clamping range S: 309 mm

recommended clamping length: 240 mm

Assembly bolt set: 269026 3

Technical description

Centre offset H base body	10 mm
System	DM
non-clamping range S	309 mm
recommended clamping length	240 mm
Assembly bolt set	269026 3
High-pressure connecting hose	269207
Plug connector for coolant connection	269208

Overall length L	808 mm
suitable interchangeable cutting heads	264838; 264839
Series	Master Mute
Boring depth up to	11×D
Vibration	damped
Through-coolant	yes
Type of product	Boring bar shanks