

**Garant**
**GARANT Master Mute boring bar shank vibration damping, 11×D, System / shank Ø: QC/25**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 264894 QC/25  |
| GTIN         | 4062406231316 |
| Item class   | 29E           |

**Description**
**Supplied with:**

Reducing adaptor for coolant connection.

**Note:**

Do not clamp on the area marked S!

$D_{\min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3.$

Convenient boring bar orientation by set-up head No. 265001.

Through-coolant: yes

System: QC

Overall length L: 330 mm

Centre offset H base body: 2.5 mm

non-clamping range S: 125 mm

recommended clamping length: 100 mm

Assembly bolt set: 269026 1

**Technical description**

|                                       |          |
|---------------------------------------|----------|
| non-clamping range S                  | 125 mm   |
| recommended clamping length           | 100 mm   |
| Centre offset H base body             | 2.5 mm   |
| System                                | QC       |
| Assembly bolt set                     | 269026 1 |
| High-pressure connecting hose         | 269207   |
| Plug connector for coolant connection | 269208   |

|  |                   |
|--|-------------------|
| Overall length L                       | 330 mm            |
| suitable interchangeable cutting heads | 264834; 264835    |
| Series                                 | Master Mute       |
| Boring depth up to                     | 11×D              |
| Vibration                              | damped            |
| Through-coolant                        | yes               |
| Type of product                        | Boring bar shanks |