

Garant
GARANT Master Mute cutting head, left-hand, System / insert size: GL/11

Order data

Order number	264831 GL/11
GTIN	4062406231484
Item class	29D

Description
Suitable for:

Boring bar shanks No. 264866, 264870 and 264874.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: GL

Cutting point / joint: 16 mm

ISO code cutting head: SDUCL

suitable indexable insert: DC.. 0702..

Approach angle: 93 °

Minimum pre-drill $\varnothing D_{\min}$: 20 mm

Centre offset L_3 : 11 mm

Technical description

Centre offset L_3	11 mm
Cutting point / joint	16 mm

Approach angle	93 °
System	GL
Series	Master Mute
suitable indexable insert	DC.. 0702..
ISO code cutting head	SDUCL
Minimum pre-drill $\varnothing D_{\min}$	20 mm
Overall length L	16 mm
Insert screw	269028 38
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Set of insert screws Type 38	269028 38
------------------------------	-----------