

Garant**GARANT Master Mute cutting head, left-hand, System / insert size: GL/10****Order data**

Order number	264831 GL/10
GTIN	4062406231477
Item class	29D

Description**Suitable for:**

Boring bar shanks No. 264866, 264870 and 264874.

Note:

Combination of all cutting heads with all boring bar shanks within the same system (GL, QC, DM) possible.

Through-coolant: yes

System: GL

Cutting point / joint: 16 mm

ISO code cutting head: SCLCL

suitable indexable insert: CC.. 0602..

Approach angle: 95 °

Minimum pre-drill $\varnothing D_{\min}$: 20 mm

Centre offset L_3 : 11 mm

Technical description

Minimum pre-drill $\varnothing D_{\min}$	20 mm
Approach angle	95 °

Overall length L	15.4 mm
Cutting point / joint	16 mm
Series	Master Mute
ISO code cutting head	SCLCL
suitable indexable insert	CC.. 0602..
Centre offset L ₃	11 mm
System	GL
Insert screw	269028 38
Application type	left-hand
Through-coolant	yes
Type of product	Cutting head

Accessories

Set of insert screws Type 38	269028 38
------------------------------	-----------