

**PRYOR****Numeral punch set, 10 pieces Mirror script 0 – 9, Character height: 5mm****Order data**

Order number	085420 5
GTIN	5022044006782
Item class	08W

**Description****Version:**

Made of hard and tough steel with particularly precise machine engraving and depth tolerance; accurately centred. Calibrated shank, through hardened. Striking head enhancement for safe working. Supplied in a plastic case.

**High performance precision punches**, chemically nickel-plated, very long service life.

**Mirror script**; i.e. the punched character appears laterally reversed on the component (for die making).

**Application:**

For punching into materials with a **strength up to 1200 N/mm<sup>2</sup>**.

**Spare part:**

Individual number punches under No. 085411 size font height/number, e. g. No. 085411 size 3/1.

Individual letter punches under No. 085431 size font height/character, e.g. No. 085431 size 3/A.

**Note:**

Other hand and machine punches of all types, such as punches with a company's logo etc., are available on request.

**Technical description**

Character height	5 mm
------------------	------

overall length	70 mm
Shank thickness	9.5
Type of product	Hand punch

---

## Accessories

Punch holder Type GRIP	085475 GRIP
------------------------	-------------