

Garant**Compact clamp, Reach A: 47mm****Order data**

Order number	370143 47
GTIN	4062406233136
Item class	31K

Description**Advantage:**

- **Compact design, dirt-repellent and chip-repellent.**
- **Height scale permits quick pre-setting of the clamping height.**
- **Captive pressure piece. Pressure piece adapters are attached by a magnetic insert.**
- **Easy assembly using the clamping arm.**

Material:

Body and pressure arm of heat treatable steel.

Supplied with:

Compact clamp, T-nut for width 14 mm and screw M12.

Optional extras:

Pressure piece set No. 370148.

Technical description

Clamping height S	0 - 90 mm
Reach A	47 mm
Length L	95 mm

Width B	40 mm
Height H	81 mm
maximum torque	105 Nm
maximum clamping force	16 kN
for thread M	M12
Type of product	Compact clamp

Accessories

Riser block for compact clamps Height H 80 mm	370146 80
Pressure piece set, 3 pieces Type 3	370148 3